
## ARCL/COML-D-AC-PATTERN-INSTALLATION



<u>SERIES</u>	DIM "A"
ARCL/COML 14-D	1 29/32"
ARCL/COML 24-D	2 3/4"
ARCL/COML 44-D	4"

NOTE: BE SURE TO REMOVE
PROTECTIVE LINER FROM LENSES
LENSES TO BE INSTALLED WITH
SMOOTH SIDE IN/TEXTURED SIDE



TO BE INSTALLED BY A
QUALIFIED ELECTRICIAN IN
ACCORDANCE TO LOCAL &
NATIONAL ELECTRIC CODES.



FAILURE TO COMPLY TO
INSTRUCTIONS &
FORMENTIONED WARNINGS
COULD VOID PRODUCT
WARRANTY



DO NOT CONNECT LED TRAY(S) WHEN UNDER LOAD.




DAY-O-LITE ASSUMES NO RESPONSIBILITIES FOR CLAIMS FOUNDED FROM IMPROPER INSTALLATION OR HANDLING.



DO NOT CONSTRUCT ROW ON FLOOR & LIFT TO CEILING.



CEILING TO BE PROPERLY REINFORCED TO SUPPORT WEIGHT OF THE FIXTURE.



MUST BE INSTALLED BY A QUALIFIED ELECTRICIAN. DISCONNECT POWER DURING INSTALLATION/SERVICING. ROW CONFIGURATION IS JOB SPECIFIC, CONSULT SHOP DRAWINGS BEFORE CONSTRUCTING ROWS. STANDARD OPTIONS/SIZES SHOWN, OTHER OPTIONS AVAILABLE WITH SIMILAIR INSTALLATION. BE SURE TO UNDERSTAND ALL PROCEDURES PRIOR TO INSTALLATION. IMPORTANT: THE NATIONAL ELECTRIC CODE REQUIRES THAT ANY FIXTURE IN EXCESS OF 50 POUNDS MUST BE INDEPENDENTLY SUPPORTED OF THE OUTLET BOX. DAY-O-LITE IS NOT RESPONSIBLE FOR INADEQUATE REINFORCEMENT OF STRUCTURAL SUPPORT SYSTEMS. DAY-O-LITE RESERVES THE RIGHT TO MAKE ANY MECHANICAL OR MATERIAL CHANGES TO THE FIXTURES WHICH DO NOT AFFECT THE APPEARANCE OR PERFORMANCE. THIS PRINT IS THE PROPERTY OF DAY-O-LITE AND THE INFORMATION IT CONTAINS MAY NOT BE USED WITHOUT WRITTEN CONSENT OF DAY-O-LITE.

MODEL NO.: ARCL/COML

ARCL/COML 24/44-D----

CONTACT INFORMATION:

126 Chestnut Street, Warwick, RI 02888
Tel. (401) 467-8232 | Fax. (401) 941-2960
E-mail: sales@dayolite.com
WWW: http://www.dayolite.com

**DAY-O-LITE**Lighting Without Limits

PAGE:

SHEET 1 OF 2

PART NUMBER: 970012A0


ISSUED ON:

10/11/19

DO NOT CONNECT LED

TRAY(S) WHEN UNDER LOAD.

## ARCL/COML-D-AC-PATTERN-INSTALLATION



<u>SERIES</u>	DIM "A"
ARCL/COML 14-D	1 29/32"
ARCL/COML 24-D	2 3/4"
ARCL/COML 44-D	4"

**NOTE: BE SURE TO REMOVE** PROTECTIVE LINER FROM LENSES LENSES TO BE INSTALLED WITH **SMOOTH SIDE IN/TEXTURED SIDE** OUT

1. REMOVE LENS AND LED TRAY. INSTALL ADJUSTABLE CABLE GRIPPER OR STEM

∠(4)1/4-20 BOLT


(4)1/4-20 NUT

2. HANG FIXTURE. INSTALL AC CABLE OR STEM IN MOUNTING LOCATIONS ACCORDING TO JOB DRAWINGS. LIFT FIXTURE INTO POSITION AND SECURE MOUNTING

3. HANG NEXT FIXTURE. CONNECT HARNESS ENDS AND JOIN TO ALREADY HUNG FIXTURE USING SUPPLIED HARDWARE. CONTINUE HANGING AND JOINING FIXTURES UNTIL ROW IS COMPLETE.

4. FEED POWER FEED CORD THROUGH FEED HOLE IN FIXTURE. USE APPROPRIATE STRAIN RELIEF TO SECURE CORD IN FIXTURE AS REQUIRED BY LOCAL ELECTRICAL CODES. CUT END FROM HARNESS AND CONNECT POWER FEED CONDUCTORS TO APPROPRIATE WIRES OF WIRE HARNESS. STANDARD WIRING DIAGRAM SHOWN, REFER TO JOB DRAWINGS FOR JOB SPECIFIC WIRING

6.REINSTALL LED TRAYS AND LENSES AFTER ALL WIRING CONNECTIONS ARE MADE AND ALL FIXTURES ARE HUNG.



POWER FEED CORD STRAIN RELIEF 4 POWER FEED > **CONDUCTORS** WIRE HARNESS (CUT END OFF FOR CONNECTION TO POWER FEED)

TO BE INSTALLED BY A QUALIFIED ELECTRICIAN IN

**ACCORDANCE TO LOCAL &** 

NATIONAL ELECTRIC CODES.

MAINS POWER FIXTURE ACCESS PLATE VIOLET = DIM+ OR POWER CABLE GREEN = GROUND BLACK = HOT (SWITCHED) WHITE = NEUTRAL LED DRIVER SINGLE CIRCUIT

MUST BE INSTALLED BY A QUALIFIED ELECTRICIAN. DISCONNECT POWER DURING INSTALLATION/SERVICING. ROW CONFIGURATION IS JOB SPECIFIC, CONSULT SHOP DRAWINGS BEFORE CONSTRUCTING ROWS, STANDARD OPTIONS/SIZES SHOWN, OTHER OPTIONS AVAILABLE WITH SIMILAIR INSTALLATION. BE SURE TO UNDERSTAND ALL PROCEDURES PRIOR TO INSTALLATION. IMPORTANT: THE NATIONAL ELECTRIC CODE REQUIRES THAT ANY FIXTURE IN EXCESS OF 50 POUNDS MUST BE INDEPENDENTLY SUPPORTED OF THE OUTLET BOX. DAY-O-LITE IS NOT RESPONSIBLE FOR INADEQUATE REINFORCEMENT OF STRUCTURAL SUPPORT SYSTEMS, DAY-O-LITE RESERVES THE RIGHT TO MAKE ANY MECHANICAL OR MATERIAL CHANGES TO THE FIXTURES WHICH DO NOT AFFECT THE APPEARANCE OR PERFORMANCE, THIS PRINT IS THE PROPERTY OF DAY-O-LITE AND THE INFORMATION IT CONTAINS MAY NOT BE USED WITHOUT WRITTEN CONSENT OF DAY-O-LITE.

MODEL NO.: ARCL/COML 24/44-D----

CONTACT INFORMATION:

126 Chestnut Street, Warwick, RI 02888 Tel. (401) 467-8232 | Fax. (401) 941-2960 E-mail: sales@davolite.com WWW: http://www.dayolite.com

Lighting Without Limits

SHEET 2 OF 2

PART NUMBER: 970012A0

ISSUED ON: 10/11/19